



Certificates, protocols and services for process sensors

	Flow sensors	Pressure sensors	Temperature sensors	Vibration sensors	Level sensors	Analytical sensors
Certificate of conformance / compliance	All series	All series	All series	All series	All series	All series
2.2 Certificate Manufacturer's certificates EN10204-2.2 Article number ZC0002	All series except SDGxx, SVxx5x	All series except PS3xxx, PS4xxx, PT05xx	All series except TA3597, TM4599, TSxxxx, TWxxxx	-	All series	-
3.1 Certificate Material certificate EN10204-3.1 Article number ZC0003	SI6xxx	PG27xx	TA20xx		LR2750	LDL100
	SF111A	PG28xx	TA22xx		LR2759	LDL101
	SF211A	PI00xA	TA25xx			
	SF311A	PI1xxx	TA28xx			
	SF121A	PI2x9x	TCCxxx			
	SF221A	PI22xx	TD2xxx			
	SF321A	PI23xx	TM45x1			
	SF120A	PI2602	TM48x1			
	SF220A	PI27xx	TM49x1			
	SF320A	PI28xx	TTx291			
		PI7x9x				
		PM1xxx				
		PY279x				
	PY9000					
<p>Aseptoflex-, G1"-, G3/4"-, G1/2"-adapters E33001-E33922, E30009, E30013, E30052, E30055, E30056, E30072, E30122, E30128, E30130, E30149, E30150, E30157, E30500, E30501, E30528-E30531, E43300-E43313, E43315, E43319, E43407, E43918-E43920</p> <p>Thermowells E30393, E30397, E30403, E37411, E37421, E37430, E37431, E37450, E37810, E37820, E37830, E37850</p> <p>E37910, E37920, E37930, E37950, E38395, E38826</p> <p>LR guided wave radar probes E43340, E43341, E43342, E43345, E43346, E43347, E43348, E43424, E43917</p>						
Calibration verification pressure Article number ZC0071	-	All series except PT05xx, PVxxxx, PSxxx	-	-	-	-
A2LA calibration 3-, 5-, and n-point Article number ZC0064, -65, -66	-	-	All series except TWxxx, TS contact sensors for solid bodies	-	-	-
ISO calibration 3-, 5-, and n-point Article number ZC0016, -17, -18	-	-	All series except TWxxx. TN7xxx, TR7xxx, TV7xxx on request	-	-	-

	Flow sensors	Pressure sensors	Temperature sensors	Vibration sensors	Level sensors	Analytical sensors
ISO calibration SD Article number ZC0020	All SD except SDGxxx, SDx1xx, SDx6xx, SDx8xx, SDxx5x, SD05xx	-	-	- - - -	-	-
ISO calibration SM Article number ZC0052	SM2xxx SM6xxx except SM6x2x SM7xxx except SM7x2x SM8xxx except SM8x2x SM9xxx	-	-	- - - -	-	-
ISO calibration SM Article number ZC0054	SM6x2x SM7x2x SM8x2x	-	-	- - -	-	-
ISO calibration SMF Article number ZC0114	SMF	-	-	-	-	-
ISO calibration SU Article number ZC0053	SUxxxx	-	-	-	-	-
Factory calibration TW Article number ZC0061	-	-	TW2xxx	-	-	-
ISO calibration LDL Article number ZC0109	-	-	-	-	-	LDL101
ISO calibration LDL Article number ZC0111	-	-	-	-	-	LDL2 / LDL4
Material inspection certificate EN10204-2.1/2.2 (non-metallic materials) EN10204-3.1 (metallic materials) Article number ZC0076	-	-	-	-	LW2	-
ISO calibration VTV / VKV Article number ZC0116	-	-	-	VTV / VKV	-	-
Cleaning service for oxygen use ANSI B40.1 Level 4 Article number ZC0070	-	≤ 363 psi (25 bar) PN, PG24., PK, PP, PT (except PT05xx), PU, PV	-	-	-	-