E12658

Connection cable


VDOAX050MSS0,25H05STGH005MSS

Article to be discontinued

Discontinuation date: 03/31/2026

Alternative articles: EVCA32

When selecting an alternative article and accessories please note that technical data may differ!



Application		
Special feature		gold-plated contacts
Design		Power cable, L-coded
Application		Industrial applications
Electrical data		
Operating voltage	[V]	63 DC
Max. current load total	[A]	16
Operating conditions		
Ambient temperature	[°C]	-40...90
Protection		IP 67
Mechanical data		
Weight	[g]	104.2
Molded-body material		TPE
Material nut		brass, nickel-plated
Sealing material		FKM
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 0.25 m, PVC/PUR, black, Ø 11.3 mm; 5 x 2.5 mm²

Electrical connection - plug

Connector: 1 x M12, straight; coding: L; Contacts: 5, gold-plated; Moulded body: TPE; Locking: brass, nickel-plated




E12658

Connection cable

VDOAX050MSS0,25H05STGH005MSS

Electrical connection - 2

Connection



Electrical connection - Socket

Connector: 1 x M12, angled; coding: L; Contacts: 5, gold-plated; Moulded body: TPE; Locking: brass, nickel-plated; sealing: FKM

