
EBC011

Splitter box

ZDO8H050MSS0000-00STAK190MSS



Application		
Special feature		Free from silicone; Gold-plated contacts
Application		Industrial applications / factory automation; Use in machine tools, coolants and lubricants
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 30 DC; ("supply class 2" to cULus)
Max. current load per module/slot	[A]	4
Max. current load total	[A]	10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67

EBC011


Splitter box

ZDO8H050MSS0000-00STAK190MSS

Tests / approvals			
UL approval		Enclosure type	Type 1
Mechanical data			
Weight	[g]	303.5	
Housing		rectangular	
Type of mounting		backplane mounting	
Dimensions	[mm]	152 x 60 x 33	
Materials		housing: PA	
Number of ports splitter box		8	
Connector type		M12	
Accessories			
Items supplied		Protective caps: 2 labels: 8	
Remarks			
Pack quantity		1 pcs.	

Electrical connection - Connection

Connector: 1 x M23; Contacts: 19, gold-plated; Tightening torque: 0.8...1.5 Nm




EBC011

Splitter box

ZDO8H050MSS0000-00STAK190MSS

Connection



Electrical connection - slot

Connector: 8 x M12; coding: A; Contacts: 5, gold-plated; Tightening torque: 0.8...1.5 Nm

