




Welding thermowell for temperature sensors

THERMOWELL, D6/WELD-IN/G1/2 conical/L=50



EC 1935/2004 EHEDG Certified FCM FCM JP FDA

Application

Design	for temperature sensors EL = 50 mm	
Pressure rating	300 bar	30 MPa

Mechanical data

Weight	[g]	159.3
Materials		stainless steel (316L/1.4404)
Sensor connection		G 1/2 sealing cone Ø 6 mm
Process connection		welding adapter Ø 34 mm
Surface characteristics Ra/Rz of the wetted parts		Ra < 0.6 µm
Installation length EL	[mm]	49
Bore length BL	[mm]	87

Remarks

Pack quantity	1 pcs.
---------------	--------