
E10154

Limit plunger

LIMIT PLUNGERS IE



1 movable bolt with spring return stroke 1.5mm, Ø 5.5mm

Application		
Design		for types, M8 x 1, Sn = 1 mm b, 2 mm b
Mechanical data		
Weight	[g]	36.6
Materials		Limit plunger: free cutting steel; plunger: steel (1.0503 / C45K) hardened on front; Lock nut: brass nickel-plated
Activation force	[N]	> 5
Remarks		
Pack quantity		1 pcs.