
# EBC022

## Splitter box

ZDO8H050MSS0005H19




| | | |
|---|---|---|
| **Application** | | |
| Special feature | | Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability |
| Application | | Industrial applications / factory automation; Use in machine tools, coolants and lubricants |
| Free from silicone | | yes |
| **Electrical data** | | |
| Operating voltage | [V] | < 30 DC;  ("supply class 2" to cULus) |
| Protection class | | II |
| Max. current load per module/slot | [A] | 4 |
| Max. current load total | [A] | 12 |
| **Operating conditions** | | |
| Ambient temperature | [°C] | -25...80 |
| Ambient temperature (moving) | [°C] | -5...60 |
| Protection | | IP 67; IP 68 |
| **Tests / approvals** | | |
| UL approval | | Enclosure type: Type 1 |
| **Mechanical data** | | |
| Weight | [g] | 906.5 |
| Housing | | rectangular |
| Type of mounting | | backplane mounting |

# EBC022

## Splitter box

ZDO8H050MSS0005H19

| | | | |
|---|---|---|---|
| Dimensions | [mm] | 127 x 54 x 22 | |
| Materials | | housing: PA | |
| Material nut | | brass, nickel-plated | |
| Number of ports splitter box | | 8 | |
| Connector type | | M12 | |
| Drag chain suitability | | yes | |
| Drag chain suitability | | bending radius for flexible use | min. 10 x cable diameter |
| | | travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s² |
| | | bending cycles | > 2 Mio. |
| | | torsional strain | ± 30 °/m |

### Accessories

| | |
|---|---|
| Items supplied | Protective caps: 2 |
| | labels: 8 |

### Remarks


| | |
|---|---|
| Pack quantity | 1 pcs. |

### Electrical connection

Cable: 5 m, PUR, Halogen-free, black, Ø 9.7 mm; 16 x 0.34 mm² (43 x Ø 0.1 mm ) + 3 x 0.75 mm² (95 x Ø 0.1 mm )

### Electrical connection - slot

Connector: 8 x M12; coding: A; Contacts: 5, gold-plated; Locking: brass, nickel-plated; Tightening torque: 0.8...1.5 Nm




# EBC022

## Splitter box

ZDO8H050MSS0005H19

### Connection




| | Core colours : |
|---|---|
| BK = | black |
| BN = | brown |
| BU = | blue |
| GN = | green |
| GY = | grey |
| PK = | pink |
| RD = | red |
| VT = | lilac |
| WH = | white |
| YE = | yellow |