
E35060


Measuring head for infrared temperature sensors

SENSOR HEAD



1 3/4" Clamp ISO 2852

Application		
Design		for infrared temperature sensors
Operating conditions		
Ambient temperature	[°C]	-20...250
Mechanical data		
Weight	[g]	169.5
Dimensions	[mm]	M30 x 1.5 / L = 64.5
Thread designation		M30 x 1.5
Materials		AlMg3 black anodised; stainless steel (303/1.4305); lock nuts: stainless steel (304/1.4301); O-ring: FKM
Lens material		front pane:tempered optical glass
Tightening torque	[Nm]	0.165
Remarks		
Pack quantity		1 pcs.
Diagrams and graphs		



1 diameter of the measured spot

2 measuring distance