
E43001

Flange plate for level sensors

FLANGE PLATE 73-90 D16



1 sealings

Application			
Design		for capacitive level sensors LK, LI, LT, LL	
Installation		according to DIN 24557	
Pressure rating		0.5 bar	0.05 MPa
Operating conditions			
Ambient temperature	[°C]	0...80	
Mechanical data			
Weight	[g]	183	
Type of mounting		according to DIN 24557	
Materials		aluminium anodised; Lock nut: stainless steel; spacing sleeve: brass; clamping ring: FKM; Sealing: NBR	
Tightening torque	[Nm]	6...9	
Sensor connection		clamp adapter Ø 16 mm	
Process connection		flange	
Remarks			
Pack quantity		1 pcs.	