
AC2267

AS-Interface control cabinet module

SmartLine25 4DI 4DO T C AUX



1 panel for labelling
2 addressing socket
3 DIN rail holder

Application		
Design		housing for DIN rail mounting, only for operation with AS-i masters with the profile M4
Application		Installation in control cabinets
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	50
Additional voltage supply	[V]	20 DC
Max. current consumption from additional supply	[mA]	4300; (AUX)
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 4; Number of digital outputs: 4
Inputs		
Number of digital inputs		4
Input circuit of digital inputs		PNP; (type 2 according to IEC 61131-2)
Sensor supply of the inputs		AUX
Voltage supply	[V]	20...30; (DC)
Max. total current rating of inputs	[mA]	200
Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes

AC2267

AS-Interface control cabinet module

SmartLine25 4DI 4DO T C AUX

Outputs						
Number of digital outputs		4				
Circuit		PNP				
Voltage range DC	[V]	20...30; (AUX)				
Max. current load per output	[mA]	1000; (utilisation category DC-12: 700 mA; utilisation category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))				
Total current rating of all outputs	[A]	4				
Short-circuit proof		yes				
Electrically separated		yes				
Actuator supply outputs		AUX				
Operating conditions						
Ambient temperature	[°C]	-25...70				
Max. relative air humidity	[%]	90; (non condensing)				
Max. height above sea level	[m]	2000				
Protection		IP 20				
Pollution degree		2				
Tests / approvals						
EMC		EN 61000-6-2				
		EN 62026-2				
		EN 50581				
MTTF	[years]	186				
Notes		The device shall be supplied from an isolating source.; This voltage source must have a secondary UL-listed fuse (see enclosed sheet).; Alternatively, a class 2 power supply can be used to supply AUX.				
AS-i classification						
AS-i version		3.0				
AS-i addressing		addressing socket				
Extended addressing mode		yes				
AS-i master profile		M4				
AS-i profile		S-7.A.7				
AS-i I/O configuration	[hex]	7				
AS-i ID code	[hex]	A.7				
AS-i certificate pending		yes				
Assignment of the data bits		data bit	D0	D1	D2	D3
		input	I-1	I-2	I-3	I-4
		Output	O-1	O-2	O-3	O-4
Mechanical data						
Weight	[g]	144.8				
Housing		rectangular				
Type of mounting		mounting on DIN rail; (TH35 (EN 60715))				
Dimensions	[mm]	93 x 25.4 x 108				
Materials		PC-GF20				

AC2267

AS-Interface control cabinet module

SmartLine25 4DI 4DO T C AUX

Displays / operating elements		
Display	switching status	LED, yellow I1...I4, O1…O4
	operation	LED, green AS-i, AUX
	errors	LED, red


Accessories	
Accessories (optional)	connectors

Remarks	
Pack quantity	1 pcs.

Electrical connection

pin header:

Connection



A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
E+	external voltage supply for sensors/actuators +24V (AUX)
E-	external voltage supply for sensors/actuators 0V (AUX)
I1...I4	switching input sensor 1...4
O-	switching output actuator 0V
O1...O4	switching output actuator 1...4