
II0340

Inductive sensor

IIK2015BABOA/SL/LS-100-AK



Product characteristics		
Output function		normally open
Sensing range	[mm]	15
Housing		threaded type
Dimensions	[mm]	M30 x 1.5 / L = 72
Application		
Special feature		Increased sensing range
Electrical data		
Operating voltage	[V]	20...250 AC/DC
Protection class		I
Reverse polarity protection		no
Outputs		
Output function		normally open
Max. voltage drop switching output DC	[V]	6
Max. voltage drop switching output AC	[V]	6.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	1 (250 V AC) / 0.8 (140 V AC) / 0.8 (24 V DC)
Permanent current rating of switching output AC	[mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC	[mA]	100
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)

II0340

Inductive sensor

IIK2015BABOA/SL/LS-100-AK

Switching frequency AC	[Hz]	25	
Switching frequency DC	[Hz]	40	
Short-circuit proof		no	
Overload protection		no	
Detection zone			
Sensing range	[mm]	15	
Operating distance	[mm]	0...12.1	
Increased sensing range		yes	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.47 / copper: 0.4	
Hysteresis	[% of Sr]	3...20	
Operating conditions			
Ambient temperature	[°C]	-25...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
MTTF	[years]	609	
Mechanical data			
Weight	[g]	231.5	
Housing		threaded type	
Mounting		flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 72	
Thread designation		M30 x 1.5	
Materials		housing: brass white bronze coated; sensing face: PBT; LED window: PA; lock nuts: brass	
Displays / operating elements			
Display		switching status	1 x LED, red
Electrical connection			
Required protection		miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting	
Accessories			
Items supplied		lock nuts: 2	
		serrated washers: 2	
Remarks			
Remarks		Recommendation: Check the safe functioning of the unit after a short circuit.	
Pack quantity		1 pcs.	

II0340


Inductive sensor

IIK2015BABOA/SL/LS-100-AK

Electrical connection - plug

Connector: 1 x 1/2"; coding: C; Contacts: 3





Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting