
DV2120

1-segment signal lamp

LED-Lamp/IO-Link



IO-Link

Application			
Application			signalling machine conditions
Electrical data			
Operating voltage	[V]		18...30 DC; (to SELV/PELV ; "supply class 2" to cURus)
Nominal voltage DC	[V]		24
Current consumption	[mA]		< 90
Switch-on peak current	[mA]		400
Switch-on peak current duration	[ms]		50
Interfaces			
Communication interface			IO-Link
Transmission type			COM2 (38,4 kBaud)
IO-Link revision			1.1
SDCI standard			IEC 61131-9
SIO mode			yes
Required master port type			A
Min. process cycle time	[ms]		8
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	1054
Operating conditions			
Ambient temperature	[°C]		-25...50
Storage temperature	[°C]		-40...75
Max. relative air humidity	[%]		90
Max. height above sea level	[m]		4000
Protection			IP 67
Pollution degree			2

DV2120


1-segment signal lamp

LED-Lamp/IO-Link

Tests / approvals		
MTTF	[years]	488
Mechanical data		
Weight	[g]	153
Dimensions	[mm]	Ø 56 / L = 61
Materials		housing: ABS; lens: PC
Displays / operating elements		
Display		LED segment, red / green / yellow / blue / lilac / cyan / white
Accessories		
Accessories (optional)		mounting base, E89060
		wall bracket, E89061
		mounting adapter, E89063
		bracket with lateral cable entry, E89064
		mounting tube, E89065
		mounting tube, E89066
		mounting tube, E89067
		mounting base, E89080
Remarks		
Remarks		For further information please see the operating instructions.
Pack quantity		1 pcs.

Electrical connection - plug

Connector: M12; coding: A; Contacts: 5



IO-Link	
1	UB+
2	not used
3	UB-
4	IO-Link
5	not used

standard mode	
1	IN1 red
2	IN2 green
3	GND
4	not used
5	IN3 blue


DV2120

1-segment signal lamp

LED-Lamp/IO-Link

Diagrams and graphs

light intensity distribution curve



light intensity distribution curve: red

1000 lm


operating efficiency = 20%

DV2120

1-segment signal lamp

LED-Lamp/IO-Link

light intensity distribution curve



light intensity distribution curve: green

1000 lm


operating efficiency = 22%

DV2120

1-segment signal lamp

LED-Lamp/IO-Link

light intensity distribution curve



light intensity distribution curve: blue

1000 lm


operating efficiency = 20%

DV2120

1-segment signal lamp

LED-Lamp/IO-Link

base mounting



1 E89080 not supplied

2 E89065, E89066, E89067 not supplied


3 E89060 not supplied

DV2120

1-segment signal lamp

LED-Lamp/IO-Link

wall mounting



1 E89080 not supplied

2 E89065, E89066, E89067 not supplied

3 E89061 not supplied