
E74205

AS-Interface flat cable

Flat cable 100 meter TPE ye



Application			
Special feature		Drag chain suitability	
Application		Industrial applications / factory automation	
Electrical data			
Operating voltage	[V]	26.5...31.6 DC; (Peak voltage 300 V)	
Operating conditions			
Ambient temperature	[°C]	-40...105	
Tests / approvals			
UL approval		AWM style	2103
		File number UL	E130266
CSA approval		file number	LL55255-42
Mechanical data			
Weight	[g]	8179	
Drag chain suitability		yes	
Drag chain suitability		bending radius for flexible use	75 mm
		travel speed	max. 4 m/s at 10 m horizontal travel length and max. acceleration of 4 m/s²
		bending cycles	≥ 10 Mio
		torsional strain	360°/m
Remarks			
Remarks		100 m supplied on a cable drum	
Pack quantity		1 pcs.	
Electrical connection			

Cable: 100 m, TPE, yellow; 2 x 1.5 mm²