
E11645

Connecting cable with socket

ADOAO140MSS0002A12



CE


Application		
Application		Industrial applications / factory automation
Electrical data		
Operating voltage	[V]	< 30 DC
Max. current load total	[A]	3
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Weight	[g]	302.65
Dimensions	[mm]	45 x 20 x 49
Moulded-body material		PUR
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 2 m, PVC/PUR, black, Ø 9.2 mm; 2 x 0.75 mm² (42 x Ø 0.15 mm) / brown, blue + 10 x 0.34 mm² (19 x Ø 0.15 mm)

Electrical connection - socket

Connector: 1 x M16, angled; Contacts: 11; Moulded body: PUR; Locking: brass, nickel-plated




E11645

Connecting cable with socket

ADOAO140MSS0002A12

Connection



M:	not used
U:	not used
	Core colours :
BK =	black
BN =	brown
BU =	blue
GN =	green
GY =	grey
PK =	pink
VT =	lilac
WH =	white
YE =	yellow
RD =	red