


IM5135



Inductive sensor

IMC4040-CPKG/K1/US-100-DPA



- 1 LED yellow
2 LED green



Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range [mm]		40
Housing		rectangular
Dimensions [mm]		40 x 40 x 54
Application		
Special feature		Correction factor K = 1; Magnetic-field immune
Magnetic-field immune		yes
Max. magnetic field immunity [mT]		300
Electrical data		
Operating voltage [V]		10...36 DC
Current consumption [mA]		< 20
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		complementary
Max. voltage drop switching output DC [V]		2.5
Max. leakage current [mA]		0.1



Inductive sensor

IMC4040-CPKG/K1/US-100-DPA

Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	200
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Sensing range	[mm]	40
Real sensing range Sr	[mm]	40 ± 10 %
Operating distance	[mm]	0...32.4

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 1 / brass: 1 / aluminium: 1 / copper: 1
Hysteresis	[% of Sr]	1...20
Switch point drift	[% of Sr]	-10...10
Correction factor K = 1		yes

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67; IP 69K

Tests / approvals

EMC	EN 61000-4-2 ESD	8 kV CD / 6 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF	[years]	972
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	voltage supply	Class 2
	File number UL	E174191

Mechanical data

Weight	[g]	134
Housing		rectangular
Sensing face		5 positions selectable
Mounting		non-flush mountable
Dimensions	[mm]	40 x 40 x 54
Materials		housing: PA; sensing face: PA black; bevelled housing part: PA; clamp: orange; screw: stainless steel (304CU/1.4567)

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Remarks

Pack quantity		1 pcs.
---------------	--	--------

IM5135



Inductive sensor

IMC4040-CPKG/K1/US-100-DPA

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4; Locking: locking, rotatable, stainless steel (316L/1.4404)



Connection

