
E70377

AS-Interface flat cable splitter

FCE Splitter ye/ye ProcessL



Application		
Design		AS-i / 24 V
Application		hygienic and wet areas in the food industry
Electrical data		
Protection class		III
Max. current load total	[A]	8
Outputs		
Electrical design		AS-i
Operating conditions		
Ambient temperature	[°C]	-30...80
Max. relative air humidity	[%]	80; (31 °C; linearly decreasing to 50 % (40 °C))
Max. height above sea level	[m]	2000
Protection		IP 67; IP 68; IP 69K
Pollution degree		2
Tests / approvals		
EMC		EN 61000-6-2
Mechanical data		
Weight	[g]	101.5
Materials		metal parts: stainless steel (316L/1.4404); rubber gasket for contact pins: FPM; O-ring: EPDM
Tightening torque	[Nm]	2.5; (lock nuts)
Accessories		
Accessories (optional)		Torque wrench, E70390
Remarks		
Pack quantity		1 pcs.