
EBC003

Splitter box

ZDO4H050MSS0000-00STAK190MSS



Application			
Special feature		Free from silicone; Gold-plated contacts	
Application		Industrial applications / factory automation; Use in machine tools, coolants and lubricants	
Free from silicone		yes	
Electrical data			
Operating voltage	[V]	< 30 DC; ("supply class 2" to cULus)	
Max. current load per module/slot	[A]	4	
Max. current load total	[A]	10	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	
Tests / approvals			
UL approval		Enclosure type	Type 1
Mechanical data			
Weight	[g]	226.5	
Housing		rectangular	

EBC003

Splitter box

ZDO4H050MSS0000-00STAK190MSS

Type of mounting		backplane mounting
Dimensions	[mm]	118.2 x 60 x 33
Materials		housing: PA
Number of ports splitter box		4
Connector type		M12

Accessories


Items supplied	Protective caps: 2
	labels: 4

Remarks

Pack quantity	1 pcs.

Electrical connection - Connection

Connector: 1 x M23; Contacts: 19, gold-plated; Tightening torque: 0.8...1.5 Nm



EBC003


Splitter box

ZDO4H050MSS0000-00STAK190MSS


Connection

AN_i_0697_M

Original Scale Drawing (MTD)



EPS Source
Product Scale Drawing
Frame Size: 36 mm x 41 mm



EBC003

Splitter box

ZDO4H050MSS0000-00STAK190MSS

Electrical connection - slot

Connector: 4 x M12; coding: A; Contacts: 5, gold-plated; Tightening torque: 0.8...1.5 Nm

