
MK5214

T-slot cylinder sensor

MKT3028BBPKG/G/WFI/0,3M/ZH/US



1 fastening clamp
2 Sensing face
3 illustration (example)

Product characteristics		
Electrical design		PNP
Output function		normally open
Dimensions	[mm]	25 x 5 x 6.5
Application		
Special feature		Magnetic-field immune
Operating principle		GMR-Zelle; suppression of extraneous fields
Application		welding applications
Magnetic-field immune		yes
Max. magnetic field immunity	[mT]	200
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 10
Protection class		III
Reverse polarity protection		yes
Max. power-on delay time	[ms]	300
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	9
Short-circuit protection		yes
Overload protection		yes

MK5214

T-slot cylinder sensor


MKT3028BBPKG/G/WFI/0,3M/ZH/US

Detection zone			
Response sensitivity	[mT]	2.8	
Travel speed	[m/s]	< 0.25	
Accuracy / deviations			
Hysteresis	[mm]	< 1.5	
Repeatability	[mm]	< 0.2	
Operating conditions			
Ambient temperature	[°C]	-25...85	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		EN 61000-4-2 ESD	- CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
		EN 55011	class B
Vibration resistance		EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
Shock resistance		EN 60068-2-27 Ea	30 g 6 shocks / 11 ms half-sine (x, y, z)
MTTF	[years]	1267	
UL approval		UL approval no.	C003
Mechanical data			
Weight	[g]	23.5	
Mounting		flush mountable	
Type of mounting		fastening clamp with combined slot / hexagon socket, width across flats 1.5	
Cylinder type		T-slot cylinders	
Dimensions	[mm]	25 x 5 x 6.5	
Materials		housing: PA; fastening clamp: stainless steel; knurled nut: PTFE coated; protective tube: PTFE coated	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Accessories			
Items supplied		rubber placeholder: 1	
		Cable clip: 1	
Remarks			
Remarks		operating voltage "supply class 2" according to cULus	
Pack quantity		1 pcs.	

Electrical connection - plug

Cable: 0.3 m, PUR; protective tube

Connector: 1 x M12; coding: A; Contacts: 4; Locking: knurled nut, rotatable



MK5214

T-slot cylinder sensor

MKT3028BBPKG/G/WFI/0,3M/ZH/US

Connection

