
EBC002

Splitter box

ZDO4H055MSS0000-00STAK120MSS



Application			
Special feature		Free from silicone; Gold-plated contacts	
Application		Industrial applications / factory automation; Use in machine tools, coolants and lubricants	
Free from silicone		yes	
Electrical data			
Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)	
Max. current load per module/slot	[A]	4	
Max. current load total	[A]	10	
Outputs			
Electrical design		PNP	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	
Tests / approvals			
UL approval		Enclosure type	Type 1

EBC002

Splitter box

ZDO4H055MSS0000-00STAK120MSS

Mechanical data		
Weight	[g]	224.5
Housing		rectangular
Type of mounting		backplane mounting
Dimensions	[mm]	118.2 x 60 x 33
Materials		housing: PA
Number of ports splitter box		4
Connector type		M12


Displays / operating elements		
Display	switching status	4 x LED, yellow
	operation	1 x LED, green

Accessories	
Items supplied	Protective caps: 2
	labels: 4


Remarks	
Pack quantity	1 pcs.

Electrical connection - Connection

Connector: 1 x M23; Contacts: 12, gold-plated; Tightening torque: 0.8...1.5 Nm



Connection



EBC002

Splitter box

ZDO4H055MSS0000-00STAK120MSS

Electrical connection - slot

Connector: 4 x M12; coding: A; Contacts: 4, gold-plated; Tightening torque: 0.8...1.5 Nm

