
E37450

Welding thermowell for temperature sensors

THERMOWELL, D6/WELD-IN/L=300



EC 1935/2004 EHEDG Certified FCM FCM JP FDA

Application			
Design		for temperature sensors EL = 350 mm	
Pressure rating		400 bar	40 MPa
Accuracy / deviations			
Max. permissible flow velocity	[m/s]	13	
Mechanical data			
Weight	[g]	1577.5	
Materials		stainless steel (316L/1.4404)	
Sensor connection		1/2" NPS Ø 6 mm suitable for G1/2 and 1/2" NPT	
Process connection		welding adapter Ø 38,1 mm	
Installation length EL	[mm]	267	
Bore length BL	[mm]	304.8	
Remarks			
Pack quantity		1 pcs.	