
E20711

Fibre optic diffuse reflection sensor

FT-11-EPV-E3/F2X0,5/2M



Application		
Function principle		Diffuse reflection sensor
Application		Small bending radius
Detection zone		
Range with fibre optic amplifier type		OB50; OBF; OCF; OO50
OB50		
Range fibre optics	[mm]	20
OBF		
Range fibre optics	[mm]	25
OCF (High Power)		
Range fibre optics	[mm]	340
OO50		
Range fibre optics	[mm]	60
Operating conditions		
Ambient temperature	[°C]	-40...70
Mechanical data		
Weight	[g]	39.5
Version of sensing head		straight
Sensing head diameter	[mm]	3
Sensing head length	[mm]	20
Total length	[mm]	2000
Min. bending radius	[mm]	10
Fibre arrangement		⦿
Core diameter	[mm]	2 x 0.5
Fibre material		PMMA
Fibre head material		stainless steel (303/1.4305)
Fibre sheath material		PE
Accessories		
Items supplied		Adapter: 1 x OCF
Accessories (optional)		Cutter for fibre optics:, E20600
Remarks		
Pack quantity		1 pcs.