
E70600

AS-Interface power distributor

QUAD AS-i Splitter Box 8A



Application		
Design		AS-i / 24 V
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current load total	[A]	8
Additional voltage supply	[V]	24 DC
Operating conditions		
Ambient temperature	[°C]	-25...75
Protection		IP 65
Mechanical data		
Weight	[g]	89.5
Materials		PA 6.6; screws: stainless steel (316L/1.4404); Nuts: stainless steel (316L/1.4404); flat cable seal: NBR
Remarks		
Pack quantity		1 pcs.