
E40104

Screw-in adapter for process sensors

ADAPTER SIL18



Application			
Application		for industrial applications	
Installation		for mounting in T-pieces	
Media		liquids and gases	
Pressure rating		300 bar	30 MPa
Tests / approvals			
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions		The compatibility between medium and product material has to be checked in all applications.	
Mechanical data			
Weight	[g]	94.8	
Type of mounting		for mounting in T-pieces	
Materials		Lock nut: stainless steel (316Ti/1.4571); Adapter: stainless steel (316L/1.4404); O-ring: FKM 70 Shore A	
Sensor connection		M18 x 1,5	
Process connection		threaded connection M26 x 1,5	
Insertion depth	[mm]	28.5; (measuring probe SID, SFD, TN)	
Remarks			
Pack quantity		1 pcs.	