
E43223

Coaxial pipe for level sensors

LR COAX TUBE NPT L1200



1 fixing bracket for centring piece

Application			
Design		for level sensors LR	
Medium temperature	[°C]	-40...200	
Pressure rating		16 bar	1.6 MPa
Vacuum resistance		-1000 mbar	-0.1 MPa
Mechanical data			
Weight	[g]	645	
Materials		Coaxial pipe: stainless steel (304/1.4301); Centring piece: PPS reinforced fibre; fixing bracket: stainless steel (301/1.4310)	
Sensor connection		threaded connection G 3/4 internal thread	
Process connection		threaded connection 3/4" NPT external thread	
Length L	[mm]	1200	
Remarks			
Pack quantity		1 pcs.	