
E43005

Flange plate for level sensors

FLANGE PLATE 100-125 D16



Application			
Design		for capacitive level sensors LK, LI, LT, LL	
Pressure rating		0.5 bar	0.05 MPa
Operating conditions			
Ambient temperature	[°C]	0...80	
Mechanical data			
Weight	[g]	252	
Materials		flange: aluminium anodised; Lock nut: stainless steel; spacing sleeve: brass; clamping ring: FKM	
Tightening torque	[Nm]	6...9	
Sensor connection		clamp adapter Ø 16 mm	
Process connection		flange	
Remarks			
Pack quantity		1 pcs.	