
E43002

Welding adapter for level sensors

WELDING ADAPTER 50/D16



Application			
Design		for capacitive level sensors LK, LI, LT, LL	
Installation		Clamp fitting	
Pressure rating		0.5 bar	0.05 MPa
Operating conditions			
Ambient temperature	[°C]	0...80	
Tests / approvals			
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions		The compatibility between medium and product material has to be checked in all applications.	
Mechanical data			
Weight	[g]	394.5	
Dimensions	[mm]	Ø 50 / L = 37.5	
Materials		flange: stainless steel; Lock nut: stainless steel; spacing sleeve: brass; clamping ring: FKM	
Tightening torque	[Nm]	6...9	
Sensor connection		Ø 16 mm	
Process connection		welding adapter Ø 50 mm	
Remarks			
Pack quantity		1 pcs.	