
EVT073

Connecting cable with plug

ASTGH040VAS0010E04



Application		
Special feature		Free from silicone; Gold-plated contacts; Drag chain suitability
Application		hygienic and wet areas in the food industry
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Protection class		II
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-25...100
Note on ambient temperature		cULus: ...50
Ambient temperature (moving)	[°C]	5...100
Note on ambient temperature (moving)		cULus: ...50
Storage temperature	[°C]	-25...55
Storage humidity	[%]	10...100
Other climatic conditions for storage according to stated class		1K22/ DIN 60721-3-1
Protection		IP 65; IP 67; IP 68; IP 69K
Mechanical data		
Weight	[g]	384.8
Dimensions	[mm]	15.5 x 15.5 x 49
Moulded-body material		PVC
Material nut		stainless steel (316L/1.4404)
Drag chain suitability		yes
Drag chain suitability		bending radius for flexible use: min. 10 x cable diameter travel speed: max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s² bending cycles: > 1 Mio. torsional strain: ± 180 °/m
Remarks		
Pack quantity		1 pcs.

EVT073

Connecting cable with plug

ASTGH040VAS0010E04

Electrical connection


Cable: 10 m, PVC, orange, Ø 4.9 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Contacts: 4, gold-plated; Moulded body: PVC, orange; Locking: stainless steel (316L/1.4404); Tightening torque: 0.6...1.5 Nm



Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white