
E12430

Connecting cable with socket

ADOGD040ZDS0002H04




CE

Application		
Special feature		Gold-plated contacts
Design		power cable, T-coded
Application		Industrial applications / factory automation
Electrical data		
Operating voltage	[V]	< 60 DC
Max. current load total	[A]	12
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 67
Mechanical data		
Weight	[g]	242.7
Dimensions	[mm]	15.4 x 15.4 x 52.8
Materials		PP
Moulded-body material		TPU
Material nut		diecast zinc, nickel-plated
Remarks		
Pack quantity		1 pcs.
Electrical connection		

Cable: 2 m, PUR, black, Ø 6.75 mm; 4 x 1.5 mm²

Electrical connection - socket

Connector: 1 x M12, straight; coding: T; Contacts: 4, gold-plated; Moulded body: TPU; Locking: diecast zinc, nickel-plated




E12430

Connecting cable with socket

ADOGD040ZDS0002H04

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white