
E11566

T-splitter

T SPLITTER M12/2XUS



Application		
Design		for pressure sensors PNI
Application		Industrial applications / factory automation
Electrical data		
Operating voltage	[V]	< 30 AC / < 36 DC
Max. current load per module/slot	[A]	3
Max. current load total	[A]	3
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 68
Mechanical data		
Weight	[g]	38.2
Materials		housing: PUR
Remarks		
Remarks		orientation connectors A/B horizontal (for a vertical sensor)
Pack quantity		1 pcs.

E11566

T-splitter


T SPLITTER M12/2XUS

Electrical connection

Connection

AN_i_0711_GG

Original Scale Drawing (MTD)



32% 312,5%

EPS Source
Product Scale Drawing
Frame Size: 75 mm x 45 mm

