
E43004

Clamp fitting for process sensors

MOUNTING ADAPTER G1



1 sealings

Application			
Design		for capacitive level sensors LK, LI, LT, LL	
Installation		Clamp fitting	
Pressure rating		0.5 bar	0.05 MPa
Operating conditions			
Ambient temperature	[°C]	0...80	
Mechanical data			
Weight	[g]	335	
Dimensions	[mm]	Ø 39 / L = 57	
Materials		flange: stainless steel; Lock nut: stainless steel; spacing sleeve: brass; clamping ring: FKM; Sealing: Tesnit	
Tightening torque	[Nm]	6...9	
Sensor connection		Ø 16 mm	
Process connection		threaded connection G 1 external thread	
Remarks			
Pack quantity		1 pcs.	