
# E37250

## Thermowell for temperature sensors

THERMOWELL, D6/1/2"NPT/L=300




| | | | |
|---|---|---|---|
| **Application** | | | |
| Design | | for temperature sensors EL = 350 mm | |
| Pressure rating | | 400 bar | 40 MPa |
| **Accuracy / deviations** | | | |
| Max. permissible flow velocity | [m/s] | 6 | |
| **Mechanical data** | | | |
| Weight | [g] | 461.5 | |
| Materials | | stainless steel (316L/1.4404) | |
| Sensor connection | | 1/2" NPS Ø 6 mm suitable for G1/2 and 1/2" NPT | |
| Process connection | | 1/2" NPT | |
| Installation length EL | [mm] | 277 | |
| Bore length BL | [mm] | 304.8 | |
| **Remarks** | | | |
| Pack quantity | | 1 pcs. | |