
EVF522

Connecting cable with plug

ASTGN040VAS0050R04



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability
Design		Ethernet cable, D-coded
Application		hygienic and wet areas in the food industry; Industrial Ethernet; CAT5/CAT5e; 100 Mbit/s
Free from silicone		yes
Electrical data		
Operating voltage	[V]	30 AC / 60 DC
Protection class		III
Max. current load total	[A]	4
Overall current rating (UL)	[A]	1.66
Operating conditions		
Ambient temperature	[°C]	-25...100
Note on ambient temperature		cRUus: ...65 °C
Ambient temperature (moving)	[°C]	0...80
Note on ambient temperature (moving)		cRUus: ...65 °C
Protection		IP 65; IP 67; IP 68; IP 69K
Mechanical data		
Weight	[g]	3287
Dimensions	[mm]	15.5 x 15.5 x 51.5
Moulded-body material		PP, Halogen-free
Material nut		stainless steel (316L/1.4404)
Drag chain suitability		yes
Drag chain suitability		bending radius for flexible use: min. 15 x cable diameter
		travel speed: max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
		bending cycles: > 1 Mio.
		torsional strain: ± 180 °/m
Remarks		
Pack quantity		1 pcs.

EVF522

Connecting cable with plug

ASTGN040VAS0050R04

Electrical connection - plug


Connector: 1 x M12, straight; coding: D; Contacts: 4, gold-plated; Moulded body: PP, Halogen-free; Locking: stainless steel (316L/1.4404); Tightening torque: 0.6...1.2 Nm; Shielded connection cable: screen connected



Electrical connection

Cable: 50 m, MPPE, Halogen-free, grey, Ø 6.5 mm, shielded; PROFINET Type C; 4 x 0.34 mm² (7 x Ø 0.25 mm)

Connection



	Core colours :
BU =	blue
OG =	orange
WH =	white
YE =	yellow