
E12481

Y-splitter


ZDO2H050MSS0000-00STGH050MSS



Application		
Special feature		Free from silicone; Gold-plated contacts
Application		Industrial applications / factory automation
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 60 DC
Max. current load per module/slot	[A]	4
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 67
Mechanical data		
Weight	[g]	24.143
Materials		housing: PUR
Material nut		diecast zinc
Connector type		M12
Remarks		
Pack quantity		1 pcs.

Electrical connection - socket C

Connector: 2 x M12; coding: A; Contacts: 4, gold-plated; Locking: diecast zinc




E12481

Y-splitter


ZDO2H050MSS0000-00STGH050MSS

Connection



Electrical connection - plug A

Connector: 1 x M12; coding: A; Contacts: 5, gold-plated; Locking: diecast zinc



Electrical connection - socket B

Connector: 2 x M12; coding: A; Contacts: 5, gold-plated; Locking: diecast zinc

