
E10802

Y-splitter

ZDO2F030MSS0000-00STGH040MSS



Application		
Special feature		Free from silicone; Gold-plated contacts
Application		Industrial applications / factory automation
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 60 DC
Protection class		III
Max. current load per module/slot	[A]	3
Max. current load total	[A]	3
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Weight	[g]	21.8
Dimensions	[mm]	15.4 x 35.4 x 39.1
Materials		PUR
Moulded-body material		PUR
Material nut		brass, nickel-plated
Connector type		M8
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated; Moulded body: PUR; Locking: brass, nickel-plated




E10802

Y-splitter

ZDO2F030MSS0000-00STGH040MSS

Electrical connection

Connection



Electrical connection - socket

Connector: 2 x M8; coding: A; Contacts: 3, gold-plated; Moulded body: PUR; Locking: brass, nickel-plated

