
EBC013

Splitter box

ZDO4H050MSS0005H07



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability
Application		Industrial applications / factory automation; Use in machine tools, coolants and lubricants
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 30 DC; ("supply class 2" to cULus)
Protection class		II
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12
Operating conditions		
Ambient temperature	[°C]	-25...80
Ambient temperature (moving)	[°C]	-5...60
Protection		IP 67; IP 68
Tests / approvals		
UL approval		Enclosure type: Type 1
Mechanical data		
Weight	[g]	537
Housing		rectangular
Type of mounting		backplane mounting
Dimensions	[mm]	82 x 54 x 22
Materials		housing: PA
Material nut		brass, nickel-plated
Number of ports splitter box		4
Connector type		M12

EBC013

Splitter box

ZDO4H050MSS0005H07

Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	bending cycles	> 2 Mio.

Accessories

Items supplied	Protective caps: 2
	labels: 4

Remarks


Pack quantity	1 pcs.

Electrical connection


Cable: 5 m, PUR, Halogen-free, black, Ø 7.5 mm; 4 x 0.34 mm² (43 x Ø 0.1 mm) + 3 x 1 mm² (55 x Ø 0.15 mm)

Electrical connection - slot

Connector: 4 x M12; coding: A; Contacts: 5, gold-plated; Locking: brass, nickel-plated; Tightening torque: 0.8...1.5 Nm



Connection



Core colours :

BN =	brown
BU =	blue
GN =	green
GY =	grey
WH =	white
YE =	yellow