
E40137

T-piece

T-PIECE R3/4-M26X1.5-R3/4



Application			
Design		for sensors and adapters with process connection M26x1,5	
Flow range	[l/min]	0...20	
Application		for industrial applications	
Media		liquids and gases	
Pressure rating		30 bar	3 MPa
Tests / approvals			
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions		The compatibility between medium and product material has to be checked in all applications.	
Mechanical data			
Weight	[g]	757.5	
Materials (wetted parts)		housing: stainless steel (316Ti/1.4571)	
Sensor connection		M26 x 1,5	
Process connection		threaded connection R 3/4	
Accessories			
Accessories (optional)		Adapter: 1 x M18 x 1,5, for direct connection of flow sensors, E40104	
Remarks			
Pack quantity		1 pcs.	