E43344

Process adapter for SMS pipe fitting

ADAPT G1/2 - SMS DN50/2"



1 Sealing edge

ADI-FREE EC 1935/2004 FCM CN FCM JP FDA

Application			
Design		with leakage port (3A)	
Pressure rating		16 bar	1.6 MPa
Tests / approvals			
Pressure equipment directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions		The compatibility between medium and product material has to be checked in all applications.	
Mechanical data			
Weight	[g]	570.5	
Material		process adapter: stainless steel (1.4435 / 316L) surface characteristics: Ra < 0,4 µm / Rz 4 µm	
Sensor connection		G 1/2 sealing cone	
Process connection		SMS pipe fitting DN50 (2")	
Surface characteristics Ra/Rz of the wetted parts		Ra < 0.8 µm / Rz = 8 µm	
Sealing		metal to PEEK	

E43344

Process adapter for SMS pipe fitting

ADAPT G1/2 - SMS DN50/2"

Hygienic equipment class to DIN 11866	H3
Remarks	
Pack quantity	1 pcs.