
E73008

Wall passage


Wall passage standard




Application		
Application		Industrial applications / factory automation
Electrical data		
Operating voltage	[V]	< 60 AC/DC
Max. current load total	[A]	8; (pin 1+3: 4 A; pin 2+4: 4 A)
Operating conditions		
Ambient temperature	[°C]	-40...85
Protection		IP 65; IP 67
Mechanical data		
Weight	[g]	24.1
Materials		brass nickel-plated; Sealing: FKM
Moulded-body material		brass, nickel-plated
Tightening torque	[Nm]	1
Remarks		
Remarks		The tightening torque for the fastening nuts is 0.6...1.0 Nm.
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Contacts: 5; Moulded body: brass, nickel-plated



Connection



E73008

Wall passage

Wall passage standard

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Contacts: 5; Moulded body: brass, nickel-plated

