
EBC012

Splitter box

ZDO8H05HMSS0000-00STAK190MSS



Application		
Special feature		Free from silicone; Gold-plated contacts
Application		Industrial applications / factory automation; Use in machine tools, coolants and lubricants
Free from silicone		yes
Electrical data		
Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Max. current load per module/slot	[A]	4
Max. current load total	[A]	10
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-25...80

EBC012


Splitter box

ZDO8H05HMSS0000-00STAK190MSS

Protection			IP 67
Tests / approvals			
UL approval		Enclosure type	Type 1
Mechanical data			
Weight	[g]		306
Housing			rectangular
Type of mounting			backplane mounting
Dimensions	[mm]		152 x 60 x 33
Materials			housing: PA
Number of ports splitter box			8
Connector type			M12
Displays / operating elements			
Display		switching status	16 x LED, yellow
		operation	1 x LED, green
Accessories			
Items supplied			Protective caps: 2
			labels: 8
Remarks			
Pack quantity			1 pcs.

Electrical connection - Connection

Connector: 1 x M23; Contacts: 19, gold-plated; Tightening torque: 0.8...1.5 Nm




EBC012

Splitter box

ZDO8H05HMSS0000-00STAK190MSS

Connection



Electrical connection - slot

Connector: 8 x M12; coding: A; Contacts: 5, gold-plated; Tightening torque: 0.8...1.5 Nm

