
# E30047

## Progressive ring fitting

PROGRESSIVE RG FITTING D6/G1/2




| | | | |
|---|---|---|---|
| **Application** | | | |
| Installation | | Progressive ring fitting | |
| Pressure rating | | 50 bar | 5 MPa |
| **Tests / approvals** | | | |
| Pressure Equipment Directive | | A possible classification to PED depends on the application and has to be carried out by the user / operator. | |
| Safety instructions | | The compatibility between medium and product material has to be checked in all applications. | |
| **Mechanical data** | | | |
| Weight | [g] | 94.2 | |
| Materials | | stainless steel (316Ti/1.4571) | |
| Sensor connection | | Ø 6 mm | |
| Process connection | | threaded connection G 1/2 | |
| **Remarks** | | | |
| Pack quantity | | 1 pcs. | |