
E37210

Thermowell for temperature sensors

THERMOWELL, D6/1/2"NPT/L=100



Application			
Design		for temperature sensors EL = 100 mm	
Pressure rating		400 bar	40 MPa
Accuracy / deviations			
Max. permissible flow velocity	[m/s]	45	
Mechanical data			
Weight	[g]	180.5	
Materials		stainless steel (316L/1.4404)	
Sensor connection		1/2" NPS Ø 6 mm suitable for G1/2 and 1/2" NPT	
Process connection		1/2" NPT	
Surface characteristics Ra/Rz of the wetted parts		0.8µm	
Installation length EL	[mm]	74	
Bore length BL	[mm]	101.6	
Remarks			
Pack quantity		1 pcs.	