

E80411



Y connection cable

Adapter cable GPIO



Application	
Application	Industrial applications
Operating conditions	
Protection	IP 65
Mechanical data	
Weight	[g] 285.7
Remarks	
Pack quantity	1 pcs.

E80411




Y connection cable

Adapter cable GPIO

Electrical connection - plug C1

Connection




E80411



Y connection cable

Adapter cable GPIO

Connector: 1 x M12, straight; Contacts: 12




- 1 OUT_CMN
- 2 OUTPUT_1
- 3 INPUT_3
- 4 INPUT_CMN
- 5 INPUT_1
- 6 GND
- 7 VCC
- 8 OUTPUT_4
- 9 OUTPUT_3
- 10 OUTPUT_2
- 11 INPUT_2
- 12 INPUT_4

Electrical connection - Socket C2

Cable: 1 m, grey

Connector: 1 x M12, straight; coding: A; Contacts: 8



Electrical connection - Socket C3

Cable: 1 m, grey

Connector: 1 x M12, straight; coding: A; Contacts: 8

