


E70224




Jumper cable with valve plug

VSTGH050MSS01,5B03VDAA041--S



Application		
Special feature	Free from silicone; Halogen-free; Gold-plated contacts	
Application	Industrial applications / factory automation	
Free from silicone	yes	
Electrical data		
Operating voltage	[V]	< 24 AC/DC
Overvoltage protection	free-wheeling diode	
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection	IP 67	
Mechanical data		
Weight	[g]	117
Materials	housing: TPU	
Moulded-body material	TPU	
Material nut	brass, nickel-plated	
Displays / operating elements		
Display	operation	1 x LED, green
Accessories		
Items supplied	screw: 1	
	panel for labelling: 1	
Remarks		
Pack quantity	1 pcs.	
Electrical connection - plug		

Connector: 1 x M12, straight; coding: A; Contacts: 3, gold-plated; Moulded body: TPU; Locking: brass, nickel-plated



E70224




Jumper cable with valve plug

VSTGH050MSS01,5B03VDAA041--S

Electrical connection

Cable: 1.5 m, PUR / PVC, Halogen-free; 3 x 0.5 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x valve type A DIN (EN 175301-803), angled; Contacts: 4, nickel-plated brass; Moulded body: TPU; Locking: brass, nickel-plated

