


Process adapter DIN 11864

ADAPT DIN11864-3-NKS-A/DN32/G1 3A



- 1 internal thread G1 Aseptoflex Vario
- 2 Leakage port
- 3 groove for O-ring 24x2
- 4 sealing area



EC 1935/2004 EHEDG Certified FCM FCM JP FDA

Application

Design	for pipes, for units with Aseptoflex Vario adapter, for pipes, DN 32 (DIN 11866, Reihe A), DN 32 (DIN 11866, Reihe A)	
Pressure rating	40 bar	4 MPa

Tests / approvals

Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	

Mechanical data

Weight [g]	130.5	
Materials (wetted parts)	stainless steel (316L/1.4435) surface characteristics: Ra < 0,4 µm / Rz = 4 µm	
Sensor connection	G 1 internal thread Aseptoflex Vario	
Process connection	Clamp DN32 Ø 50.5 mm DIN 11864-3-A-NKS	
Sealing	Gasket	
Hygienic equipment class to DIN 11866	H4	

Accessories

Items supplied	O-Ring: 1 x (24 x 2 mm), EPDM, E30054	
Accessories (optional)	O-Ring: 1 x (24 x 2 mm), FKM, E30123	
	O-Ring: 1 x (24 x 2 mm), EPDM, FCM China, E30163	
	Dichtungsring: 1, PEEK, E30124	

Remarks

Pack quantity	1 pcs.
---------------	--------