


E33401



Process adapter Tri-Clamp

ADAPT G1/2-CLAMP DIN32676/1



CRN EC 1935/2004 FCM CN FCM JP FDA Hygienic Cleanable

Application			
Pressure rating	25 bar	2.5 MPa	
MAWP (for applications according to CRN) [bar]	25		
Tests / approvals			
Pressure equipment directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.		
Safety instructions	The compatibility between medium and product material has to be checked in all applications.		
Mechanical data			
Weight [g]	204.5		
Material	stainless steel (1.4435 / 316L)		
Sensor connection	G 1/2 sealing cone		
Process connection	Clamp DN25...DN40 (1...1,5") DIN 32676 (ISO 2852)		
Suitable for process connections in accordance with the standards	DIN 32676 Reihe A (DIN)	clamp DN25, DN32, DN40	
	DIN 32676 Reihe B (ISO)	clamp DN26,9, DN33,7	
	DIN 32676 Reihe C (ASME BPE)	clamp 1", 1,5"	
	ISO 2852	clamp DN25, DN33,7, DN38	
Surface characteristics Ra/Rz of the wetted parts	Ra < 0.4 µm / Rz = 4 µm		
Remarks			
Pack quantity	1 pcs.		