




AS-Interface flat cable splitter

FC Splitter AS-i UL



Electrical data		
Protection class		III
Max. current load total	[A]	8
Outputs		
Electrical design		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...75
Storage temperature	[°C]	-25...85
Protection		IP 67
Mechanical data		
Weight	[g]	49.6
Material		PBT; screw: stainless steel (1.4305 / 303); contact pins: gold-plated
Tightening torque	[Nm]	1.65; (Mounting screw)
Accessories		
Accessories (optional)		flat cable end seal:, E70413
		Heat-shrink cap:, E70113
Remarks		
Remarks		The flat cable must not end in the splitter.
		Use a flat cable seal or heat-shrink cap for sealing.
Pack quantity		1 pcs.