

CR2520



I/O module for mobile machines


R360/HIGH CURRENT MODULE/CAN

phase-out article

Alternative articles: CR0708
or CR0709

When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.



Electrical data		
Operating voltage	[V]	10...32 DC
Inputs / outputs		
Total number of inputs and outputs		30
Number of inputs and outputs		Number of digital inputs: 15; Number of analogue inputs: 4; Number of digital outputs: 15; Number of outputs with H-bridge: 4
Inputs		
Number of digital inputs		15
Number of analogue inputs		4
Analogue input (current)	[mA]	0...20
Analogue input (voltage)	[V]	0...32
Outputs		
Number of digital outputs		15
Number of PWM outputs		3
Number of outputs with H-bridge		4
Number of high-current outputs		4
Software / programming		
Parameter setting options		input/output functions
Interfaces		
Number of CAN interfaces		1

CR2520



I/O module for mobile machines

R360/HIGH CURRENT MODULE/CAN

Tests / approvals		
MTTF	[years]	66
Mechanical data		
Weight	[g]	136.5
Housing		rectangular
Type of mounting		screw mounting
Dimensions	[mm]	153 x 241 x 43
Remarks		
Notes		Please do not use for new projects.
Pack quantity		1 pcs.
Electrical connection		
AMP connector:		