




Process adapter DIN 11864

ADAPT DIN11864-3-BKS-A/DN40 3A



- 1 Aseptoflex Vario
- 2 Leakage port
- 3 sealing area



EC 1935/2004 EHEDG Certified FCM FCM JP FDA

Application

Design	with leakage port (3A)	
Pressure rating	40 bar	4 MPa

Tests / approvals

Pressure equipment directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	

Mechanical data

Weight	[g]	266
Materials (wetted parts)	stainless steel (1.4435 / 316L) surface characteristics: Ra < 0,4 µm / Rz = 4 µm	
Sensor connection	G 1 Internal thread Aseptoflex Vario	
Process connection	Clamp DN40 Ø 64 mm DIN 11864-3-A-BKS	
Sealing	Gasket	
Hygienic equipment class to DIN 11866	H4	

Accessories

Items supplied	O-Ringe: 1 x (24 x 2 mm), EPDM, E30054	
Accessories (optional)	O-Ring: 1 x (24 x 2 mm), FKM, E30123	
	O-Ring: 1 x (24 x 2 mm), EPDM, FCM China, E30163	
	Dichtungsring: 1, PEEK, E30124	

E33308



Process adapter DIN 11864

ADAPT DIN11864-3-BKS-A/DN40 3A

Remarks	
Pack quantity	1 pcs.