




Process adapter Tri-Clamp

ADAPT IFM-CLAMP ISO2852 1-1.5"



ADI-FREE CRN EC 1935/2004 FCM FCM JP FDA Hygienic Cleanable

Application			
Pressure rating	16 bar		1.6 MPa
Tests / approvals			
Pressure equipment directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.		
Safety instructions	The compatibility between medium and product material has to be checked in all applications.		
Mechanical data			
Weight	[g]	100.5	
Materials (wetted parts)	stainless steel (1.4435 / 316L) surface characteristics: Ra < 0,4 µm / Rz = 4 µm		
Sensor connection	G 1 Internal thread Aseptoflex Vario		
Process connection	Clamp DN25...DN40 (1...1,5") Ø 50.5 mm DIN 32676 (ISO 2852)		
Suitable for process connections in accordance with the standards	DIN 32676 Reihe A (DIN)	clamp DN32, DN40	
	DIN 32676 Reihe B (ISO)	clamp DN33,7	
	DIN 32676 Reihe C (ASME BPE)	clamp 1,5"	
	ISO 2852	clamp DN33,7, DN38	
Sealing	Gasket		
Hygienic equipment class to DIN 11866	H4		
Accessories			
Items supplied	O-Ringe: 1 x (24 x 2 mm), EPDM, E30054		
Accessories (optional)	O-Ring: 1 x (24 x 2 mm), FKM, E30123		
	O-Ring: 1 x (24 x 2 mm), EPDM, FCM China, E30163		
	Dichtungsring: 1, PEEK, E30124		
Remarks			
Pack quantity	1 pcs.		