




Process adapter Tri-Clamp

ADAPT IFM-CLAMP ISO2852 2" 3A



- 1 Leakage port
- 2 sealing area
- 3 Aseptoflex Vario



CRN EC 1935/2004 EHEDG Certified FCM FCM JP FDA

Application

Design	with leakage port (3A)	
Pressure rating	16 bar	1.6 MPa

Tests / approvals

Pressure equipment directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	

Mechanical data

Weight	[g]	226.5		
Materials (wetted parts)		stainless steel (1.4435 / 316L) surface characteristics: Ra < 0,4 µm / Rz = 4 µm		
Sensor connection		G 1 Internal thread Aseptoflex Vario		
Process connection		Clamp DN50 (2") Ø 64 mm DIN 32676 (ISO 2852)		
Suitable for process connections in accordance with the standards		DIN 32676 Reihe A (DIN)	clamp DN50	
		DIN 32676 Reihe B (ISO)	clamp DN42,4, DN48,3	
		DIN 32676 Reihe C (ASME BPE)	clamp 2"	
		ISO 2852	clamp DN40, DN51	
Sealing		Gasket		
Hygienic equipment class to DIN 11866		H4		

Accessories

Items supplied	O-Ringe: 1 x (24 x 2 mm), EPDM, E30054
----------------	--

E33209



Process adapter Tri-Clamp

ADAPT IFM-CLAMP ISO2852 2" 3A

Accessories (optional)	O-Ring: 1 x (24 x 2 mm), FKM, E30123
	O-Ring: 1 x (24 x 2 mm), EPDM, FCM China, E30163
	Dichtungsring: 1, PEEK, E30124
Remarks	
Pack quantity	1 pcs.