


E11807



Female cordset

ADOGH080MSS0005H08

For 8-wire cordsets the core colors are not standardized.
Please note the wiring of the sensor and the cordsets (see data sheet).



Application	
Application	Industrial applications
Electrical data	
Operating voltage	[V] < 30 AC / < 36 DC
Operating conditions	
Ambient temperature	[°C] -25...80
Protection	IP 68
Mechanical data	
Weight	[g] 313.7
Dimensions	[mm] 15 x 15 x 43
Material	PUR
Molded-body material	PUR
Material nut	brass, nickel-plated
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 5 m, PUR, black, Ø 6.2 mm; 8 x 0.25 mm²	
Electrical connection - Socket	
Connector: 1 x M12, straight; coding: A; Contacts: 8; Moulded body: PUR; Locking: brass, nickel-plated; Tightening torque: 0.7...0.9 Nm	


E11807



Female cordset

ADOGH080MSS0005H08

Connection



Colors to DIN EN 60947-5-2

Core colors :

- | | |
|------|--------|
| BK = | black |
| BN = | brown |
| BU = | blue |
| GY = | grey |
| PK = | pink |
| OG = | orange |
| VT = | lilac |
| WH = | white |